



Order form
Orderer

Valid from June 2016
Order no.

HM70 Hand-held Humidity and Temperature Meter

		HM70								PRICE
Indicator type	no indicator * rechargeable with Euro AC-adapter rechargeable with UK AC-adapter rechargeable with US AC-adapter rechargeable with AUS AC-adapter rechargeable with all AC-adapters alkaline batteries only	A B C D E F K								
Indicator accessories	no indicator accessories <i>MI70LINK software with RS232 cable (MI70LINK)</i> <i>analog output-signal cable (27168ZZ)</i> <i>MI70Link with RS232 and analog output signal cables</i> <i>MI70LINK software with USB cable (219687)</i>	0 1 2 3 4								
Probe type	<i>HMP75</i> <i>HMP75B (chemical purge and sensor preheating)</i> <i>HMP76</i> <i>HMP76B (chemical purge and sensor preheating)</i> <i>HMP77</i> <i>HMP77B (chemical purge and sensor preheating)</i>	A F B C D E								
Calibration	at room temperature	1								
Probe accessories	no accessories <i>probe holder for HMP76/76B **</i>		A B							
Connection cable to a transmitter	no connection cable <i>connection cable to HMD/W60/70 series (HMA6070)</i> <i>connection cable to HMP230 series / HMP228 (27159ZZ)</i> <i>connection cable to 20/30 series transmitters (HMA2030)</i> <i>connection cable to HMT330 and HMT120/130 (211339)</i> <i>connection cable to HMW90 (219980)</i>	0 1 2 3 4 6								
Carrying case	no carrying case <i>weather proof carrying case for MI70 and probe (HMP75/77) (MI70CASE3)</i> <i>weather proof carrying case for MI70 and long probe (HMP76) (MI70CASE4)</i> <i>soft carrying case for MI70 and short probe (HMP75/77) (MI70SOFTCASE)</i>		A D E F							
Manual language	No manual English		A B							
									TOTAL	
									QTY	
									TOTAL VALUE	

* select item A, if only probe is ordered

** used in field calibration of duct 60/70 and 20/30 transmitters

*** aluminium case for HMP76 probe (long case)

Selections in bold are included in the prices of the basic versions.

Selections in italic are available at an extra price.

Example of order code with typical settings:

HM70 B 4 A 1 A 0 D B

End customer: _____

Accessories:

Connection cable to HMT330 and HMT120/130
Connection cable to HMT310
Connection cable to HMD/W60/70 series
Connection cable to HMW90
Weather proof carrying case for MI70 and short probe
Weather proof carrying case for MI70 and long probe
Soft carrying case for MI70 and short probe
MI70LINK software with USB cable
MI70LINK software with serial port cable
Analog output cable
Probe cable extension, 10 m

Order code:

211339
DRW216050
HMA6070
219980
MI70CASE3
MI70CASE4
MI70SOFTCASE
219687
MI70LINK
27168ZZ
213107SP